

Product data sheet

Specifications

SQUARE D



8903L electrically held lighting contactor, 3 P, 3 NO, 30 A, 600 V, 110/120 V 50/60 Hz coil, NEMA 4/4X, stainless steel

8903LW30V02C

Discontinued

Discontinued on: Dec 12, 2019

End-of-service on: Oct 15, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| | |
|---------------------------|--------------------------------------|
| Product Or Component Type | Electrically Held Lighting Contactor |
| Range Of Product | 8903L |
| Control Circuit | Separate control circuit |

Complementary

| | |
|---------------------------------|-----------------------------------|
| Control Circuit Voltage | 110 V AC 50 Hz 120 V AC 60 Hz |
| Inrush Power In Va | 150 VA 60 Hz 150 VA 50 Hz |
| Hold-In Power Consumption In Va | 30 VA 60 Hz 30 VA 50 Hz |
| Current Rating | 20 A tungsten 30 A fluorescent |
| Number Of Poles | 3P 3 NO |
| Control Unit | Selector switch HAND-OFF-AUTO) |
| Pilot Light | No indicator |
| Electrical Connection | Screw-clamp terminals |
| Height | 14.69 in (373 mm) |
| Depth | 7.80 in (198 mm) |
| Width | 12.64 in (321 mm) |

Environment

| | |
|------------------------|---|
| Enclosure Type | NEMA 4/4X brushed stainless steel surface |
| Product Certifications | UL Listed CSA |

Ordering and shipping details

| | |
|-------------------|-------------------------|
| Category | 21321 - 8903 L (NOT LX) |
| Discount Schedule | CP1 |
| Returnability | No |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|-------------------|----|
| Country Of Origin | MX |
|-------------------|----|

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 14.69 in (37.3 cm) |
| Package 1 Width | 12.64 in (32.1 cm) |
| Package 1 Length | 7.80 in (19.8 cm) |
| Package 1 Weight | 22.00 lb(US) (9.98 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

| | | |
|---|------------------------------------|-----|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |
| ✓ | Pvc Free | |
| ✓ | Halogen Free Plastic Parts Product | |

Certifications & Standards

| | |
|---------------------------|---|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| California Proposition 65 | WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov |