





Contactor, Type L, multipole lighting, electrically held, 30A, 3 pole, 600 V, 110/120 VAC 50/60 Hz coil, NEMA 4/4X

8903LWW30V02

! To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Product Or Component Type	Electrically Held Lighting Contactor
Range Of Product	8903L
Control Circuit	Separate control circuit

## Complementary

,		
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz	
Inrush Power In Va	150 VA 60 Hz 140 VA 50 Hz	
Hold-In Power Consumption In Va	30 VA 60 Hz 30 VA 50 Hz	
Current Rating	20 A tungsten 30 A fluorescent	
Number Of Poles	3P 3 NO	
Control Unit	No control units	
Pilot Light	No indicator	
Electrical Connection	Screw-clamp terminals	
Height	13.07 in (332 mm)	
Depth	7.05 in (179 mm)	
Width	8.50 in (216 mm)	

### **Environment**

Enclosure Type	NEMA 4/4X glass polyester surface
<b>Product Certifications</b>	UL Listed CSA

# Ordering and shipping details

Category	21321 - 8903 L (NOT LX)	
Discount Schedule	CP1	
Returnability	No	
Country Of Origin	MX	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	13.07 in (33.2 cm)	
Package 1 Width	8.50 in (21.6 cm)	
Package 1 Length	7.05 in (17.9 cm)	
Package 1 Weight	65.87 lb(US) (29.88 kg)	

# **Contractual warranty**

Warranty 18 months

May 11, 2024



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>②</b>	Reach Free Of Svhc
<b>9</b>	Toxic Heavy Metal Free
<b>Ø</b>	Mercury Free
<b>9</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free
<b>9</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations