





Contactor, Type L, multipole lighting, mechanically held, 30A, 4 pole, 600 V, 110/120 VAC 50/60 Hz coil, NEMA 1, +option

8903LXG40V02CP21R6



! To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Product Or Component Type	Mechanically Held Lighting Contactor	
Range Of Product	8903LX	
Control Circuit	Separate control circuit	

### Complementary

•	•	
Control Voltage	110 V AC 50 Hz 120 V AC 60 Hz	
Inrush Power In Va	150 VA 60 Hz 150 VA 50 Hz 170 VA 50/60 Hz	
Current Rating	20 A tungsten 30 A fluorescent	
Number Of Poles	4P 4 NO	
Control Unit	Selector switch HAND-OFF-AUTO)	
Pilot Light	Red indicator on incandescent push-to-test	
Other Options	2P relay (1 NO + 1 NC)	
Electrical Connection	Screw-clamp terminals	
Height	11.89 in (302 mm)	
Depth	7.44 in (189 mm)	
Width	11.89 in (302 mm)	

### **Environment**

Enclosure Type	NEMA 1 painted sheet steel surface
<b>Product Certifications</b>	UL Listed CSA

## Ordering and shipping details

Category	21322 - 8903 LX (NOT L)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	44.49 lb(US) (20.18 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>②</b>	Mercury Free
<b>9</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free
<b>9</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov