

Product data sheet

Specifications



8903LX mechanically held lighting contactor, 4 P, 4 NO, 30 A, 600 V, 277/120 V 60 Hz, NEMA 1

8903LXG40V85CFF4P51P52R62T

Price*: 3,195.00 USD

! Discontinued

Main

Product Or Component Type	Mechanically Held Lighting Contactor
Range Of Product	8903LX
Control Circuit	Control circuit transformer

Complementary

Control Voltage	120 V AC 60 Hz secondary circuit 277 V AC 60 Hz primary circuit
Inrush Power In Va	150 VA 60 Hz 170 VA 50/60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number Of Poles	4P 4 NO
Control Unit	Selector switch HAND-OFF-AUTO)
Pilot Light	Red indicator on LED Green indicator off LED
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Other Options	3-wire long-distance control interface
Electrical Connection	Screw-clamp terminals
Height	11.89 in (302 mm)
Depth	7.44 in (189 mm)
Width	11.89 in (302 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months