

# Product data sheet

Specifications

SQUARE D



panelboard lighting, 100 AMP, 3 pole, panel mount, 240/277V 60Hz coil, repair

8903PBQ11V39R

Discontinued

## Main

Product	Mechanically Held Lighting Contactor
Type	PB
Control Circuit	Common control circuit

## Complementary

Control Circuit Voltage	240/277 V AC 60 Hz
Line Rated Current	100 A
Number Of Poles	3P
Awg Gauge	AWG 1/0 aluminium/copper)power AWG 18...AWG 10 copper)control
Maximum Overall Voltage	600 V AC
Auxiliary Contact Composition	Without
Mounting Support	panel
Electrical Connection	Lugs
Height	11.73 in (298 mm)
Depth	3.86 in (98 mm)
Width	7.52 in (191 mm)

## Environment

Product Certifications	UL Listed CSA
------------------------	------------------

## Ordering and shipping details

Category	21323-8903 PB
Discount Schedule	CP1
Returnability	No
Country Of Origin	US

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.