

Product data sheet

Specifications

SQUARE D



panelboard lighting cont, 200
AMP, 3 pole, bus mount, 120V
60Hz coil, repair

8903PBV11BV02R

Discontinued

Main

Product	Mechanically Held Lighting Contactor
Type	PB
Control Circuit	Common control circuit

Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Line Rated Current	200 A
Number Of Poles	3P
Awg Gauge	350 kcmil aluminium/copper)power AWG 18...AWG 10 copper)control
Maximum Overall Voltage	600 V AC
Auxiliary Contact Composition	Without
Mounting Support	busbar
Electrical Connection	Busbar connection
Height	9.49 in (241 mm)
Depth	3.39 in (86 mm)
Width	7.52 in (191 mm)

Environment

Product Certifications	UL Listed CSA
------------------------	------------------

Ordering and shipping details

Category	21323-8903 PB
Discount Schedule	CP1
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.