

Product data sheet

Specifications

SQUARE D



panelboard lighting cont, 225
AMP, 3 pole, bus mount, 240/277
60Hz coil, repair

8903PBW11BV39R

! Discontinued

Main

| | |
|-----------------|--------------------------------------|
| Product | Mechanically Held Lighting Contactor |
| Type | PB |
| Control Circuit | Common control circuit |

Complementary

| | |
|-------------------------------|--|
| Control Circuit Voltage | 240/277 V AC 60 Hz |
| Line Rated Current | 225 A |
| Number Of Poles | 3P |
| Awg Gauge | 350 kcmil aluminium/copper)power AWG 18...AWG 10 copper)control |
| Maximum Overall Voltage | 600 V AC |
| Auxiliary Contact Composition | Without |
| Mounting Support | busbar |
| Electrical Connection | Busbar connection |
| Height | 9.49 in (241 mm) |
| Depth | 3.39 in (86 mm) |
| Width | 7.52 in (191 mm) |

Environment

| | |
|------------------------|------------------|
| Product Certifications | UL Listed CSA |
|------------------------|------------------|

Ordering and shipping details

| | |
|-------------------|----------------------------|
| Category | 99999-DEFAULT ADD CATEGORY |
| Discount Schedule | N/A |
| Returnability | No |
| Country Of Origin | US |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications