

Product data sheet

Specifications

SQUARE D



lighting contactor, electrically held,
30 A, 4 pole, NEMA 12, 120/110V
60/50Hz

8903SMA3V02CNX20

! Discontinued on: Aug 17, 2021

! Discontinued

Price*: 1,565.00 USD

Main

| | |
|---------|--------------------------------------|
| Product | Electrically Held Lighting Contactor |
| Type | S |

Complementary

| | |
|-------------------------|--------------------------------------------|
| Control Circuit Voltage | 120 V AC 60 Hz 110 V AC 50 Hz |
| Current Rating | 30 A |
| Number Of Poles | 4P |
| Control Units | Selector switch 3 positions HAND-OFF-AUTO) |
| Pilot Light | Without pilot light |
| Auxiliary Contacts | 2 NO |
| Other Options | Solid neutral terminal block |
| Electrical Connection | Lugs |
| Height | 15.98 in (406 mm) |
| Depth | 7.87 in (200 mm) |
| Width | 14.88 in (378 mm) |

Environment

| | |
|------------------------|---------------------------------------------|
| Enclosure Type | NEMA 12/3R painted sheet steel surface none |
| Product Certifications | UL Listed CSA |

Ordering and shipping details

| | |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability | No |
| Country Of Origin | US |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications