

# Product data sheet

Specifications

SQUARE D



NIGHT-MASTER, combo lighting  
contactor, 30 A, 3P, fuse, NEMA  
3R, 277V 60Hz

8903SMC61V04G101

Price\*: 2,412.00 USD

! Discontinued

## Main

Type	Night-Master
------	--------------

## Complementary

Control Circuit Voltage	277 V AC 60 Hz
Current Rating	30 A
Number Of Poles	3P
Auxiliary Contacts	Without
Disconnecter Device Type	Fusible disconnect switch R, 30 A 600 V
Electrical Connection	Lugs
Height	23.50 in (597 mm)
Depth	10.51 in (267 mm)
Width	15.00 in (381 mm)

## Environment

Enclosure Type	NEMA 3R painted sheet steel surface photoelectric receptacle with cell
Product Certifications	UL listed file E16151 CCN NRNT

## Ordering and shipping details

Discount Schedule	CP1
Returnability	No

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	105.00 lb(US) (47.627 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.