

Product data sheet

Specifications

SQUARE D



Contactor, NIGHT MASTER, combination lighting, 30A, 3 pole, fuse, 110/120 VAC 50/60 Hz coil. NEMA 3R, +options

8903SMC61V81FF4G101T

Price*: 3,110.00 USD

Main

Type	Night-Master
------	--------------

Complementary

Control Circuit Voltage	480 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Current Rating	30 A
Number Of Poles	3P
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit
Disconnecter Device Type	Fusible disconnect switch R, 30 A 600 V
Electrical Connection	Lugs
Height	23.50 in (597 mm)
Depth	10.51 in (267 mm)
Width	15.00 in (381 mm)

Environment

Enclosure Type	NEMA 3R painted sheet steel surface photoelectric receptacle with cell
Product Certifications	UL listed file E16151 CCN NRNT

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.