

Product data sheet

Specifications



NIGHT-MASTER, combo lighting contactor, 30 A, 3P, fuse, NEMA 3R, 480-120V 60Hz

8903SMC63V81C6C33FF4G101T

⚠ Discontinued on: Oct 11, 2021

⚠ Discontinued

Main

Type Night-Master

Complementary

Control Circuit Voltage 480 V AC 60 Hz primary circuit
120 V AC 60 Hz secondary circuit

Current Rating 30 A

Number Of Poles 3P

Control Units Key-operated selector switch ON-OFF)

Pilot Light Without pilot light

Auxiliary Contacts Without

Control Circuit Fusing 2 fuses primary circuit

Electrical Connection Lugs

Height 38.86 in (987 mm)

Depth 10.43 in (265 mm)

Width 15.00 in (381 mm)

Environment

Enclosure Type NEMA 3R painted sheet steel surface photoelectric receptacle with cell

Product Certifications UL listed file E16151 CCN NRNT

Ordering and shipping details

Category 21326-8903 S*C

Discount Schedule CP1

Returnability No

Contractual warranty

Warranty 18 months

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.