

Product data sheet

Specifications

SQUARE D



NIGHT-MASTER, combo lighting
contactor, 30A, 3P, breaker,
NEMA 3R, 480-120V 60Hz

8903SMC81V81FF4T

Price*: 3,176.00 USD

! Discontinued

Main

Type	Night-Master
------	--------------

Complementary

Control Circuit Voltage	480 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Current Rating	30 A
Number Of Poles	3P
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit
Other Options	None
Disconnecter Device Type	Thermal magnetic circuit breaker, 30 A 600 V
Electrical Connection	Lugs
Height	23.50 in (597 mm)
Depth	10.51 in (267 mm)
Width	15.00 in (381 mm)

Environment

Enclosure Type	NEMA 3R painted sheet steel surface none
Product Certifications	UL listed file E16151 CCN NRNT

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	105.00 lb(US) (47.627 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications