

Product data sheet

Specifications

SQUARE D



lighting contactor, mechanically held, 30 A, 2 pole, NEMA 1, 120/110V 60/50Hz

8903SMG10V02A3X11

Price*: 1,389.00 USD

! Discontinued

Main

Product	Mechanically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	30 A
Number Of Poles	2P
Control Units	Push-button ON-OFF)
Pilot Light	Without pilot light
Auxiliary Contacts	1 NO + 1 NC
Other Options	None
Electrical Connection	Lugs
Height	14.13 in (359 mm)
Depth	9.72 in (247 mm)
Width	8.11 in (206 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	18.00 lb(US) (8.165 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------