

# Product data sheet

Specifications

SQUARE D



lighting contactor, mechanically held, 30 A, 4 pole, NEMA 1, 240/220V 60/50Hz

8903SMG12V03X11

Price\*: 1,139.00 USD

Discontinued

## Main

Product	Mechanically Held Lighting Contactor
Type	S

## Complementary

Control Circuit Voltage	240 V AC 60 Hz 220 V AC 50 Hz
Current Rating	30 A
Number Of Poles	4P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	1 NO + 1 NC
Other Options	None
Electrical Connection	Lugs
Height	10.00 in (254 mm)
Depth	5.28 in (134 mm)
Width	5.98 in (152 mm)

## Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product Certifications	UL Listed CSA

## Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	6.00 lb(US) (2.722 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------