

Product data sheet

Specifications

SQUARE D



lighting contactor, electrically held,
30 A, 3 pole, NEMA 1, 120/110V
60/50Hz

8903SMG2V02CFP21X11

Price*: 1,479.00 USD

! Discontinued

Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	30 A
Number Of Poles	3P
Control Units	Selector switch 3 positions HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent push-to-test
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	1 fuse
Other Options	None
Electrical Connection	Lugs
Height	10.00 in (254 mm)
Depth	5.28 in (134 mm)
Width	5.98 in (152 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications