

Product data sheet

Specifications

SQUARE D



lighting contactor, electrically held,
30 A, 5 pole, NEMA 1, 480-120V
60Hz

8903SMG4V81CFF4T

Price*: 1,863.00 USD

! Discontinued

Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	480 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Current Rating	30 A
Number Of Poles	5P
Control Units	Selector switch 3 positions HAND-OFF-AUTO)
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Other Options	None
Electrical Connection	Lugs
Height	15.87 in (403 mm)
Depth	5.20 in (132 mm)
Width	6.34 in (161 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	50.00 lb(US) (22.68 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------