

Product data sheet

Specifications

SQUARE D



lighting contactor, electrically held,
30 A, 5 pole, NEMA 1, 277-120V
60Hz

8903SMG4V85CF4NP2T

Price*: 1,998.00 USD

! Discontinued

Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	277 V AC 60 Hz priority circuit 120 V AC 60 Hz secondary circuit
Current Rating	30 A
Number Of Poles	5P
Control Units	Selector switch 3 positions HAND-OFF-AUTO)
Pilot Light	Green indicator off incandescent
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit
Other Options	Solid neutral terminal block
Electrical Connection	Lugs
Height	14.13 in (359 mm)
Depth	7.56 in (192 mm)
Width	14.88 in (378 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	30.73 lb(US) (13.939 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------