

Product data sheet

Specifications

SQUARE D



lighting contactor, mechanically held, 60 A, 3 pole, NEMA 12, 120/110V 60/50Hz

8903SPA11V02F4Y145

Discontinued on: Aug 17, 2021

Discontinued

Price*: 2,484.00 USD

Main

Product	Mechanically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	60 A
Number Of Poles	3P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses
Other Options	Coil transient suppression module
Electrical Connection	Lugs
Height	15.98 in (406 mm)
Depth	9.29 in (236 mm)
Width	8.11 in (206 mm)

Environment

Enclosure Type	NEMA 12/3R painted sheet steel surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.