

Product data sheet

Specifications

SQUARE D



lighting contactor, electrically held,
60 A, 3 pole, NEMA 12, 120/110V
60/50Hz

8903SPA2V02G101P21

Discontinued on: Aug 17, 2021

Discontinued

Price*: 2,177.00 USD

Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	60 A
Number Of Poles	3P
Control Units	No control units
Pilot Light	Red indicator on incandescent push-to-test
Auxiliary Contacts	Without
Other Options	None
Electrical Connection	Lugs
Height	15.98 in (406 mm)
Depth	9.29 in (236 mm)
Width	8.11 in (206 mm)

Environment

Enclosure Type	NEMA 12/3R painted sheet steel surface photoelectric receptacle with cell
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications