

Product data sheet

Specifications

SQUARE D



lighting contactor, electrically held,
60 A, 4 pole, NEMA 12, 480-120V
60Hz

8903SPA3V81FF4G26T

⚠ Discontinued on: Aug 17, 2021

⚠ Discontinued

Price*: 2,456.00 USD

Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	480 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Current Rating	60 A
Number Of Poles	4P
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Electrical Connection	Lugs
Height	15.75 in (400 mm)
Depth	7.87 in (200 mm)
Width	14.88 in (378 mm)

Environment

Enclosure Type	NEMA 12/3R painted sheet steel surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.