

# Product data sheet

Specifications

SQUARE D



lighting contactor, mechanically held, 100A, 3 pole, NEMA 12, 480-120V 60Hz

8903SQA11V81A3FF4T

Discontinued on: Aug 17, 2021

Discontinued

Price\*: 4,014.00 USD

## Main

|         |                                      |
|---------|--------------------------------------|
| Product | Mechanically Held Lighting Contactor |
| Type    | S                                    |

## Complementary

|                         |  |
|-------------------------|--|
| Control Circuit Voltage | 480 V AC 60 Hz primary circuit<br>120 V AC 60 Hz secondary circuit |
| Current Rating          | 100 A  |
| Number Of Poles         | 3P   |
| Control Units           | Push-button ON-OFF)  |
| Pilot Light             | Without pilot light  |
| Auxiliary Contacts      | Without  |
| Control Circuit Fusing  | 2 fuses primary circuit<br>1 fuse secondary circuit                |
| Other Options           | None   |
| Electrical Connection   | Lugs   |
| Height                  | 31.50 in (800 mm)  |
| Depth                   | 9.25 in (235 mm)   |
| Width                   | 18.15 in (461 mm)  |

## Environment

|                        |   |
|------------------------|---|
| Enclosure Type         | NEMA 12/3R painted sheet steel surface none |
| Product Certifications | UL Listed<br>CSA                            |

## Ordering and shipping details

|                   |     |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability     | No  |
| Country Of Origin | US  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications