

Product data sheet

Specifications

SQUARE D



CONTACTOR 600VAC 50AMP DPA +OPTIONS

8910DPA53V09DFG1Y135

! Discontinued

Main

Device Short Name	DPA
-------------------	-----

Complementary

Line Rated Current	50 A
Depth	3.67 in (93.22 mm)
Height	4.06 in (103.12 mm)
Locked Rotor Rated Current	300 A 230 V AC 250 A 460 V AC 200 A 575 V AC
Maximum Horse Power Rating	3 hp 115 V AC, 1 phase 10 hp 230 V AC, 1 phase 15 hp 230 V AC, 3 phase 30 hp 460/575 V AC, 3 phase
Mounting Support	panel
Number Of Poles	3
Width	2.56 in (65.02 mm)

Environment

Product Certifications	UL listed file E42240 CCN NLDX CSA LR25490 class 3211 04
------------------------	---

Ordering and shipping details

Category	21345-8910 DPA 5_(50 AMP)
Discount Schedule	CP1B
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov