

# Product data sheet

Specifications



Contactor, Definite Purpose, 60A, 3 pole, 30HP at 575VAC, 3 phase, 440/480VAC 50/60Hz coil, open

8910DPA63V06

Product availability: Stock - Normally stocked in distribution facility

Price\*: 248.50 USD

## Main

|                           |                            |
|---------------------------|----------------------------|
| Product Or Component Type | Definite Purpose Contactor |
| Line Rated Current        | 60 A                       |
| Number Of Poles           | 3P                         |
| Pole Contact Composition  | 3 NO                       |
| Range Of Product          | DPA                        |

## Complementary

|                                |                                                                                                                                    |
|--------------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| Maximum Horse Power Rating     | 5 hp 115 V AC, 1 phase<br>10 hp 230 V AC, 1 phase<br>30 hp 460 V AC, 3 phase<br>30 hp 575 V AC, 3 phase<br>25 hp 230 V AC, 3 phase |
| Locked Rotor Rated Current     | 360 A 277 V AC<br>300 A 460 V AC<br>240 A 575 V AC                                                                                 |
| [Ue] Rated Operational Voltage | 600 V AC                                                                                                                           |
| [Uc] Control Circuit Voltage   | 440 V AC 50 Hz<br>480 V AC 60 Hz                                                                                                   |
| Phase                          | 3 phase                                                                                                                            |
| Electrical Connection          | Box lugs<br>Quick connect terminals                                                                                                |
| Height                         | 4.13 in (105 mm)                                                                                                                   |
| Width                          | 2.56 in (65 mm)                                                                                                                    |
| Depth                          | 3.66 in (93 mm)                                                                                                                    |

## Environment

|                        |                      |
|------------------------|----------------------|
| Product Certifications | UL Recognized<br>CSA |
|------------------------|----------------------|

## Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US1CP1B21346 |
| Discount Schedule | CP1B         |
| Gtin              | 785901081135 |
| Returnability     | Yes          |
| Country Of Origin | MX           |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type Of Package 1       | PCE                  |
| Number Of Units In Package 1 | 1                    |
| Package 1 Height             | 3.80 in (9.652 cm)   |
| Package 1 Width              | 4.30 in (10.922 cm)  |
| Package 1 Length             | 2.70 in (6.858 cm)   |
| Package 1 Weight             | 25.76 oz (730.284 g) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

|                                                                                                              |                                                                                                                        |
|--------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------|
|  Mercury Free               |                                                                                                                        |
|  Rohs Exemption Information | <a href="#">Yes</a>                                                                                                    |
| Reach Regulation                                                                                             | <a href="#">REACH Declaration</a>                                                                                      |
| Eu Rohs Directive                                                                                            | Compliant with Exemptions                                                                                              |
| China Rohs Regulation                                                                                        | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information. |

Dimensions Drawings

Approximate Dimensions

