

Product data sheet

Specifications



Contactor, Definite Purpose, 75A, 3 pole, 40 HP at 575 VAC, 3 phase, 24/24 VAC 50/60 Hz coil, open

8910DPA73RV14

Product availability: Stock - Normally stocked in distribution facility

Price*: 318.00 USD

Main

Product Or Component Type	Definite Purpose Contactor
Line Rated Current	75 A
Number Of Poles	3P
Pole Contact Composition	3 NO
Range Of Product	DPA

Complementary

Maximum Horse Power Rating	5 hp 115 V AC, 1 phase 15 hp 230 V AC, 1 phase 25 hp 230 V AC, 3 phase 40 hp 460 V AC, 3 phase 40 hp 575 V AC, 3 phase
Locked Rotor Rated Current	450 A 277 V AC 375 A 460 V AC 300 A 575 V AC
[Ue] Rated Operational Voltage	600 V AC
[Uc] Control Circuit Voltage	24 V AC 50/60 Hz
Phase	3 phase
Electrical Connection	Box lugs Quick connect terminals
Height	3.65 in (92.8 mm)
Width	4.10 in (104.03 mm)
Depth	2.56 in (65 mm)

Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details

Category	US1CP1B21347
Discount Schedule	CP1B
Gtin	785901768579
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	US
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.06 in (10.3 cm)
Package 1 Width	3.35 in (8.5 cm)
Package 1 Length	3.66 in (9.3 cm)
Package 1 Weight	24.00 oz (680.4 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.