

Product data sheet

Specifications

SQUARE D



Contactor, Definite Purpose, 90A, 3 pole, 50 HP at 575 VAC, 3 phase, 110/120 VAC 50/60 Hz coil, open

8910DPA93V02

Product availability : Stock - Normally stocked in distribution facility

Price* : 400.38 USD

Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	90 A
Number of Poles	3P
Pole contact composition	3 NO
Range of Product	DPA

Complementary

Maximum Horse Power Rating	7.5 hp 115 V AC, 1 phase 20 hp 230 V AC, 1 phase 30 hp 230 V AC, 3 phase 50 hp 460 V AC, 3 phase 50 hp 575 V AC, 3 phase
Locked rotor rated current	540 A 277 V AC 450 A 460 V AC 360 A 575 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Phase	3 phase
Electrical Connection	Quick connect terminals Box lugs
Height	5.26 in (133.60 mm) 5.28 in (134 mm)
Width	3.39 in (86.11 mm) 3.39 in (86 mm)
Depth	4.67 in (118.62 mm)
Net Weight	3.70 lb(US) (1.68 kg) 3.7 lb(US) (1.68 kg)

Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details

Category	21349-8910 DPA 9_(90 AMP)
Discount Schedule	CP1B

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

GTIN	785901118398
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	5.50 in (13.97 cm)
Package 1 Width	5.70 in (14.478 cm)
Package 1 Length	7.00 in (17.78 cm)
Package 1 Weight	3.70 lb(US) (1.678 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)