

# Product data sheet

Specifications

**SQUARE D**



Contactor, Definite Purpose, 90A, 3 pole, 50 HP at 575 VAC, 3 phase, 208/240 VAC 60 Hz 220 VAC 50 Hz coil, open

8910DPA93V09

**Product availability : Stock - Normally stocked in distribution facility**

**Price\* : 400.38 USD**

## Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	90 A
Number of Poles	3P
Pole contact composition	3 NO
Range of Product	DPA

## Complementary

Maximum Horse Power Rating	7.5 hp 115 V AC, 1 phase 20 hp 230 V AC, 1 phase 30 hp 230 V AC, 3 phase 50 hp 460 V AC, 3 phase 50 hp 575 V AC, 3 phase
Locked rotor rated current	540 A 277 V AC 450 A 460 V AC 360 A 575 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	208...240 V AC 60 Hz 220 V AC 50 Hz
Phase	3 phase
Electrical Connection	Quick connect terminals Box lugs

## Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

## Ordering and shipping details

Category	21349-8910 DPA 9_(90 AMP)
Discount Schedule	CP1B
GTIN	785901118404
Returnability	Yes
Country of origin	CN

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	6.00 in (15.24 cm)
Package 1 Width	5.50 in (13.97 cm)
Package 1 Length	7.00 in (17.78 cm)
Package 1 Weight	3.61 lb(US) (1.638 kg)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
RoHS exemption information	Yes

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)