

Product data sheet

Specifications



Starter, Definite Purpose, nonreversing, 50A, 3 pole, 3 phase, 208V to 240V AC coil, melting alloy overload, NEMA 1

8911DPSG53V09

Product availability: Stock - Normally stocked in distribution facility

Price*: 752.75 USD

Main

Product	Definite Purpose Starter
Ampere Rating	50 A
Horsepower Rating	3 hp 115 V AC, 1 phase 10 hp 230 V AC, 1 phase 15 hp 230 V AC, 3 phase 30 hp 460 V AC, 3 phase 30 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	220 V AC 50 Hz 208...240 V AC 60 Hz
Phase	3 phase

Complementary

Enclosure Material	Painted sheet steel
Enclosure Rating	NEMA 1
Locked Rotor Amperes	300 A 230 V AC 250 A 460 V AC 200 A 575 V AC
Number Of Poles	3P
Range	DPS
Overload Type	Melting alloy
Number Of Thermal Units	3

Ordering and shipping details

Category	US10CP121381
Discount Schedule	0CP1
Gtin	785901025108
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	7.20 in (18.288 cm)
Package 1 Width	7.50 in (19.05 cm)
Package 1 Length	20.50 in (52.07 cm)
Package 1 Weight	9.50 lb(US) (4.309 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information.