

Product data sheet

Specifications



NEMA starter, Definite Purpose, 20A, 7.5HP at 600VAC, 3 phase, 3 pole, melting alloy, 120VAC coil, open

8911DPSO13V02

Product availability: Stock - Normally stocked in distribution facility

Price*: 321.20 USD

Main

Product	Definite Purpose Starter
Ampere Rating	20 A
Horsepower Rating	3 hp 230 V AC, 1 phase 7.5 hp 230 V AC, 3 phase 1.5 hp 115 V AC, 1 phase 7.5 hp 460 V AC, 3 phase 7.5 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Phase	3 phase

Complementary

Enclosure Rating	Not rated (open device)
Locked Rotor Amperes	120 A 230 V AC 100 A 460 V AC 80 A 575 V AC
Number Of Poles	3P
Range	DPS
Overload Type	Melting alloy
Number Of Thermal Units	3

Ordering and shipping details

Category	US10CP121381
Discount Schedule	0CP1
Gtin	785901116752
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.70 in (11.938 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	4.80 in (12.192 cm)
Package 1 Length	7.70 in (19.558 cm)
Package 1 Weight	2.26 lb(US) (1.025 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.