

Product data sheet

Specifications

SQUARE D



NEMA starter, Definite Purpose, 20A, 7.5HP at 600VAC, 3 phase, 3 pole, melting alloy, 24VAC coil, open

8911DPSO13V14

Discontinued

Discontinued on: Sep 15, 2023

To be end-of-service on: Dec 31, 2024

Product availability: Stock - Normally stocked in distribution facility

Main

Product	Definite Purpose Starter
Ampere Rating	20 A
Horsepower Rating	3 hp 230 V AC, 1 phase 7.5 hp 230 V AC, 3 phase 1.5 hp 115 V AC, 1 phase 7.5 hp 460 V AC, 3 phase 7.5 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	24 V AC 50/60 Hz
Phase	3 phase

Complementary

Enclosure Rating	Not rated (open device)
Locked Rotor Amperes	120 A 230 V AC 100 A 460 V AC 80 A 575 V AC
Number Of Poles	3P
Range	DPS
Overload Type	Melting alloy
Number Of Thermal Units	3

Ordering and shipping details

Category	US10CP121381
Discount Schedule	0CP1
Gtin	785901025153
Returnability	Yes
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	5.00 in (12.7 cm)
Package 1 Width	5.00 in (12.7 cm)
Package 1 Length	8.00 in (20.32 cm)
Package 1 Weight	2.45 lb(US) (1.111 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information.