



# Definite Purpose Starter (Type: DPS) 30A, 2-Pole, 1-Phase, Open

8911DPSO32V06

- Discontinued on: Nov 12, 2020
- ! End-of-service on: Dec 31, 2020

! Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product	Definite Purpose Starter
Ampere Rating	30 A
Horsepower Rating	2 hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Phase	1 phase

# Complementary

Enclosure Rating	Not rated (open device)
Locked Rotor Amperes	180 A 230 V AC
	150 A 460 V AC
	120 A 575 V AC
Number Of Poles	2P
Range	DPS
Overload Type	Melting alloy
Number Of Thermal Units	1

# Ordering and shipping details

Category	US10CP121381
Discount Schedule	0CP1
Gtin	00785901932109
Returnability	No
Country Of Origin	MX

### **Contractual warranty**

Warranty 18 months

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# Sustainability

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >

# Well-being performance

Mercury Free	
Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.