

# Product data sheet

Specifications

SQUARE D



## Definite Purpose Starter (Type: DPS) 40A, 3-Pole, 3-Phase, Open

8911DPSO43V07

⚠ Discontinued on: Jun 30, 2020

⚠ Discontinued

### Main

Product	Definite Purpose Starter
Ampere Rating	40 A
Horsepower Rating	3 hp 115 V AC, 1 phase 10 hp 230 V AC, 3 phase 7.5 hp 230 V AC, 1 phase 20 hp 460 V AC, 3 phase 25 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	550 V AC 50 Hz 600 V AC 60 Hz
Phase	3 phase

### Complementary

Enclosure Rating	Not rated (open device)
Locked Rotor Amperes	240 A 230 V AC 200 A 460 V AC 160 A 575 V AC
Number Of Poles	3P
Range	DPS
Overload Type	Melting alloy
Number Of Thermal Units	3

### Ordering and shipping details

Category	21381-8911 DP
Discount Schedule	CP1
Gtin	785901227984
Returnability	No
Country Of Origin	CN

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.00 in (12.7 cm)
Package 1 Width	5.00 in (12.7 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	8.00 in (20.32 cm)
Package 1 Weight	2.36 lb(US) (1.071 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
Eu Rohs Directive	Compliant	<a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>	Product out of China RoHS scope. Substance declaration for your information.