

Product data sheet

Specifications



Pump Panel, NEMA Type S, Well Guard, Size 1, 27A, 10HP, 5kA SSCR, 30A fuse clip, Motor Logic SSOLR, 440/480VAC 50/60Hz coil, NEMA 3R

8940SSC4010

Product availability: Stock - Normally stocked in distribution facility

Price*: 2,003.00 USD

Main

Product	Well-Guard Control
Type	class 8940 type SS
Device Application	Pumping

Complementary

Control Circuit Type	Common control circuit
Control Circuit Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Line Rated Current	27 A
Number Of Poles	3
Horsepower Rating	10 hp 480 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO) Push-button START)
Disconnect Type	Fusible disconnect switch
Associated Fuse Rating	30 A
Fuse Type	H or K
Thermal Overload Type	Motor Logic solid state class 10/20
Protection Type	Overload Phase loss Phase unbalance
Device Mounting	Surface
Electrical Connection	Screw terminal
Nema Size	1
Height	39.06 in (992 mm)
Width	15.16 in (385 mm)
Depth	9.69 in (246 mm)

Environment

Nema Rating	NEMA 3R
-------------	---------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Enclosure Type	Weatherproof enclosure indoor/outdoor
Product Certifications	UL Listed NEMA

Ordering and shipping details

Category	US10CP121388
Discount Schedule	0CP1
Gtin	785901011781
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.00 in (25.4 cm)
Package 1 Width	18.40 in (46.736 cm)
Package 1 Length	36.60 in (92.964 cm)
Package 1 Weight	58.00 lb(US) (26.308 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	8
Package 2 Height	42.00 in (106.68 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	509.46 lb(US) (231.086 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Pvc Free

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Not compliant

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information.

California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov