

Product data sheet

Specifications



Pump Panel, NEMA Type S, Well Guard, Size 4, 135A, 10kA SSCR, 100HP, 200A Class H and K fuse clip, Motor Logic SSOLR, 480VAC 60Hz coil, NEMA 3R

8940SSF4100

Product availability: Stock - Normally stocked in distribution facility

Price*: 7,718.00 USD

Main

Product	Well-Guard Control
Type	class 8940 type SS
Device Application	Pumping

Complementary

Control Circuit Type	Common control circuit
Control Circuit Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Line Rated Current	135 A
Number Of Poles	3
Horsepower Rating	100 hp 480 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO) Push-button START)
Disconnect Type	Fusible disconnect switch
Associated Fuse Rating	200 A
Fuse Type	H or K
Thermal Overload Type	Motor Logic solid state class 10/20
Protection Type	Overload Phase loss Phase unbalance
Device Mounting	Surface
Electrical Connection	Screw terminal
Nema Size	4
Height	49.02 in (1245 mm)
Width	20.55 in (522 mm)
Depth	10.35 in (263 mm)

Environment

Nema Rating	NEMA 3R
-------------	---------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Enclosure Type	Weatherproof enclosure indoor/outdoor
Product Certifications	UL Listed NEMA

Ordering and shipping details

Category	US10CP121389
Discount Schedule	0CP1
Gtin	785901011828
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.60 in (32.0 cm)
Package 1 Width	22.01 in (55.9 cm)
Package 1 Length	50.31 in (127.8 cm)
Package 1 Weight	140.00 lb(US) (63.503 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Pvc Free

Reach Regulation	REACH Declaration
Eu Rohs Directive	Not compliant
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov