

Product data sheet

Specifications



HOIST CONTACTOR 600VAC 30A DPR

8965DPR33V06

Discontinued on: Jul 12, 2021

Discontinued

Main

Product Or Component Type	Reversing Hoist Contactor
Line Rated Current	30 A
Maximum Horse Power Rating	2 hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase 10 hp 230 V AC, 3 phase 15 hp 460 V AC, 3 phase 15 hp 575 V AC, 3 phase

Complementary

Product Certifications	CSA UL Listed
[Ue] Rated Operational Voltage	600 V AC
Poles Description	3P
[Uc] Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Phase	3 phase
Range Of Product	DPR

Ordering and shipping details

Category	21403-8965DPR1>DPR4 - 20A>40A REV HOIST
Discount Schedule	CP1
Gtin	00785901769903
Returnability	No
Country Of Origin	CN

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Mercury Free	
<hr/>		
	Rohs Exemption Information	Yes
<hr/>		
Eu Rohs Directive		Compliant
		EU RoHS Declaration
<hr/>		
China Rohs Regulation		China RoHS declaration
		Product out of China RoHS scope. Substance declaration for your information.
<hr/>		