# Product data sheet

Specifications



Illuminated selector switch, Harmony 9001K, metal, long handle, green, 30mm, 2 positions, stay put, 110-120V, 1 C/O

9001K11J1FGH13

① Discontinued

() Discontinued on: Mar 8, 2023

# Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Illuminated selector switch	
Device Short Name	К	
Type Of Operator	maintained	
Operator Profile	gloved hand knob	

### Complementary

Bezel Material	Metal	
Mounting Diameter	1.18 in (30 mm)	
Operator Position Information	2 positions	
Contacts Type And Composition	1 C/O	
Connections - Terminals	Screw-clamp terminals, 1 x 0.222 x 1.5 mm <sup>2</sup> IEC 60947-1	
Device Presentation	Complete product	
Cap/Operator Or Lens Colour	Green	
[Us] Rated Supply Voltage	110120 V	
Light Block Supply	Via integral transformer	
Operator Profile	Long handle	
Type Of Operator	Stay put	
Supply Frequency	5060 Hz	
Size	30 mm	
Bulb Base	BA 9s	
Light Source	Incandescent bulb	
Cam Profile	5	

#### Environment

Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

## Ordering and shipping details

Category	US10CS121426	
Discount Schedule	0CS1	
Gtin	785901550655	
Returnability	No	
Country Of Origin	MX	

## **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	5.08 in (12.903 cm)	
Package 1 Width	2.00 in (5.08 cm)	
Package 1 Length	12.90 in (32.774 cm)	
Package 1 Weight	8.80 oz (249.476 g)	

### **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information
Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov