

# Product data sheet

Specifications

SQUARE D



## SELECTOR SWITCH 600VAC 10A 30MM T-K

9001K43J38GH13

⚠ Discontinued on: Oct 11, 2019

⚠ Discontinued

### Main

Range Of Product	Harmony 9001K
Product Or Component Type	Selector switch
Device Short Name	K
Type Of Operator	maintained
Operator Profile	standard knob

### Complementary

Bezel Material	Chromium plated metal
Mounting Diameter	1.18 in (30 mm)
Operator Position Information	3 positions
Connections - Terminals	Screw-clamp terminals, 1 x 0.22...2 x 1.5 mm <sup>2</sup> IEC 60947-1
Device Presentation	Complete product

### Environment

Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	UL listed file E42259 CCN NKCR CE CSA LR24590 class 3211 03

### Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Returnability	No
Country Of Origin	MX

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.