





30mm push button, Type K, pilot light, blue 24/28VAC/VDC LED light module, blue plastic fresnel lens, NEMA 4, 13

9001KP35LLL31

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 153.00 USD

### Main

Range Of Product	Harmony 9001K
Product Or Component Type	Pilot light
Device Short Name	9001K

### Complementary

Bezel Material	Metal
Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Round
Lens Type	Domed plastic
Cap/Operator Or Lens Colour	Blue
Light Source	Blue LED
Bulb Base	BA 9s
Light Block Supply	Direct 2428 V AC/DC
Connections - Terminals	Screw clamp terminals, 1 x 0.222 x 1.5 mm² IEC 60947-1
Tightening Torque	7.08 lbf.in (0.8 N.m) IEC 60947-1
Shape Of Screw Head	Cross slotted
Operating Position	Any position
[Ui] Rated Insulation Voltage	250 V 2)IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	2.5 kV IEC 60947-1
Short-Circuit Protection	10 A cartridge fuse IEC 60947-5-1
Light Source	LED
[Ith] Conventional Free Air Thermal Current	10 A
Cad Overall Width	2.13 in (54 mm)
Cad Overall Height	2.76 in (70 mm)
Cad Overall Depth	1.65 in (42 mm)
Net Weight	0.30 lb(US) (0.134 kg)
Lens Type	Fresnel
[Us] Rated Supply Voltage	2428 V

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Light Source Colour	Blue
Lens Material	Polycarbonate
Size	30 mm

### **Environment**

Livitoiiiieit	
Standards	EN/IEC 60947-5-1 JIS C8201-5-1 EN/IEC 60947-1 EN/IEC 60947-5-4 UL 508 CSA C22.2 No 14 JIS C 852 JIS C8201-1
Product Certifications	UL 508 NEMA
Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27
Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 3R NEMA 4 NEMA 6

# Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901457480
Returnability	No
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.08 in (12.903 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)
Package 1 Weight	8.00 oz (226.796 g)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov