# Product data sheet

Specifications





# PILOT LIGHT 28V 30MM TYPE K +OPTIONS

9001KP35LYA31

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 153.00 USD

#### Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Pilot light	
Device Short Name	9001K	

#### Complementary

e emprementar j		
Bezel Material	Chromium plated metal	
Mounting Diameter	1.18 in (30 mm)	
Shape Of Signaling Unit Head	Round	
Lens Type	Domed plastic	
Cap/Operator Or Lens Colour	Amber	
Light Source	Yellow LED	
Bulb Base	BA 9s	
Light Block Supply	Direct 2428 V AC/DC	
Connections - Terminals	Screw clamp terminals, 1 x 0.222 x 1.5 mm² IEC 60947-1	
Tightening Torque	7.08 lbf.in (0.8 N.m) IEC 60947-1	
Shape Of Screw Head	Cross slotted	
Operating Position	Any position	
[Ui] Rated Insulation Voltage	250 V 2)IEC 60947-1	
[Uimp] Rated Impulse Withstand Voltage	2.5 kV IEC 60947-1	
Short-Circuit Protection	10 A cartridge fuse IEC 60947-5-1	
[Ith] Conventional Free Air Thermal Current	10 A	
Cad Overall Width	2.13 in (54 mm)	
Cad Overall Height	2.76 in (70 mm)	
Cad Overall Depth	1.65 in (42 mm)	
Net Weight	0.30 lb(US) (0.134 kg)	

### Environment

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Standards	EN/IEC 60947-5-4 JIS C8201-5-1 UL 508 CSA C22.2 No 14 EN/IEC 60947-1 JIS C 852 EN/IEC 60947-5-1 JIS C8201-1	
Product Certifications	UL 508 NEMA	
Protective Treatment	TC	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6	
Shock Resistance	50 gn IEC 60068-2-27	
Overvoltage Category	Class II IEC 61140	
Ip Degree Of Protection	IP66 IEC 60529	
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 4 NEMA 6	

# Ordering and shipping details

Category	US10CS121426	
Discount Schedule	0CS1	
Gtin	785901177289	
Returnability	Yes	
Country Of Origin	MX	

### **Packing Units**

0	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.81 in (4.600 cm)
Package 1 Width	2.16 in (5.499 cm)
Package 1 Length	3.66 in (9.299 cm)
Package 1 Weight	8.00 oz (226.800 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	16
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	8.44 lb(US) (3.829 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	512

Package 3 Height	29.53 in (75.000 cm)	
Package 3 Width	31.50 in (80.000 cm)	
Package 3 Length	23.62 in (60.000 cm)	
Package 3 Weight	287.75 lb(US) (130.522 kg)	

### **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information
Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov