Product data sheet

Specifications



() Discontinued

round pilot light Ø 30 - clear - LED BA 9s - 120 V AC/DC - IP66

9001KP38LYC6

- () Discontinued on: Dec 2, 2020
- (!) End-of-service on: Dec 31, 2020

Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Pilot light	
Device Short Name	9001K	

Complementary

Bezel Material	Chromium plated metal	
Mounting Diameter	1.18 in (30 mm)	
Shape Of Signaling Unit Head	Round	
Lens Type	Domed glass	
Cap/Operator Or Lens Colour	Clear	
Light Source	Yellow LED	
Bulb Base	BA 9s	
Light Block Supply	Direct 120 V AC/DC	
Connections - Terminals	Screw clamp terminals, 1 x 0.222 x 1.5 mm ² IEC 60947-1	
Tightening Torque	7.08 lbf.in (0.8 N.m) IEC 60947-1	
Shape Of Screw Head	Cross slotted	
Operating Position	Any position	
[Ui] Rated Insulation Voltage	250 V 2)IEC 60947-1	
[Uimp] Rated Impulse Withstand Voltage	2.5 kV IEC 60947-1	
Short-Circuit Protection	10 A cartridge fuse IEC 60947-5-1	
[Ith] Conventional Free Air Thermal Current	10 A	
Cad Overall Width	2.13 in (54 mm)	
Cad Overall Height	2.76 in (70 mm)	
Cad Overall Depth	1.65 in (42 mm)	
Net Weight	0.30 lb(US) (0.134 kg)	

Environment

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Standards	EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60947-1 JIS C8201-5-1 JIS C 852 EN/IEC 60947-5-4 UL 508 JIS C8201-1
Product Certifications	NEMA UL 508
Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27
Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 4 NEMA 6

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov