

# Product data sheet

Specifications

SQUARE D



## PUSHBUTTON OPERATOR 30MM TYPE K +OPTIONS

9001KR141E12

 **Discontinued on:** Dec 19, 2019

 **Discontinued**

### Main

Bezel Material	Chromium plated metal
Control Button Type	key operated push-button
Device Short Name	K
Enclosure Type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Light Source	without
Mounting Diameter	1.18 in (30 mm)
Operator Additional Information	Full guard in metal

### Complementary

Contacts Type And Composition	Without contact block
Control Type	push-button
Key Number	E12
Light Block Supply	Without supply Without supply
Marking	unmarked
Mounting Support	panel
Operator Position Information	3 positions
Operator Profile	1 projecting push-button
Shape	Round head
Type Of Operator	Lockable test button extended position locked or unlocked position
Utilisation Category	AC-15 DC-13

### Environment

Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

### Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Gtin	00785901959038

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	MX

### Contractual warranty

Warranty	18 months
----------	-----------