## Product data sheet

Specifications





# 30mm Push Button, Type K, push button, no guard, universal

9001KR3U

Product availability: Stock - Normally stocked in distribution facility

Price\*: 38.60 USD

## Main

Range Of Product	Harmony 9001K
Product Or Component Type	Head for push-button
Device Short Name	9001K
Operator Profile	projecting, unmarked
Operator Additional Information	Without guard

## Complementary

Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Round
Type Of Operator	spring return
Net Weight	0.20 lb(US) (0.09 kg)
Bezel Material	Metal
Cap/Operator Or Lens Colour	7 colours choice
Operator Profile	Projecting
Type Of Operator	Spring return
Contacts Type And Composition	Without contact block

## Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901874911
Returnability	Yes
Country Of Origin	MX

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.00 in (5.08 cm)
Package 1 Width	2.30 in (5.842 cm)
Package 1 Length	2.80 in (7.112 cm)
Package 1 Weight	3.68 oz (104.326 g)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 2	PAL
Number Of Units In Package 2	3200
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	766.00 lb(US) (347.451 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information


Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)				
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.				
Circularity Profile	No need of specific recycling operations				
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov				

## **Dimensions Drawings**

## **Dimensions**




## 9001KR3U

## Mounting and Clearance

## **Contact Block Mounting Position**


Top and Rear views



- (1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)
- (2) Operator
- (3) Locating notch
- (4) Side 1
- (5) Side 2

## Panel Cut-Out

#### Clearance



Legend plate	a min.		b min.	
	mm	in.	mm	in.
9001KN2••	57.2	2.25	44.5	1.75
9001KN3••	57.2	2.25	50.8	2.00

#### **Individual Cut-outs Details**

2 alternatives

