

# Product data sheet

Specifications



## PUSH BUTTON 600VAC 10A 30MM T-K

9001KR5RH18

Discontinued on: Oct 11, 2019

Discontinued

### Main

|                   |                       |
|-------------------|-----------------------|
| Bezel Material    | Chromium plated metal |
| Device Short Name | K                     |
| Mounting Diameter | 1.18 in (30 mm)       |

### Complementary

|                               |                          |
|-------------------------------|--------------------------|
| Line Rated Current            | 10 A                     |
| Contacts Type And Composition | 1 NO + 4 NC              |
| Operator Position Information | 2 positions              |
| Operator Profile              | 1 projecting push-button |
| Utilisation Category          | DC-13<br>AC-15           |

### Environment

|                           |                                                                   |
|---------------------------|-------------------------------------------------------------------|
| Nema Degree Of Protection | NEMA 1/2/3/3R/4/6/12/13                                           |
| Product Certifications    | CSA LR24590 class 3211 03<br>UL listed file E42259 CCN NKCR<br>CE |

### Ordering and shipping details

|                   |                             |
|-------------------|-----------------------------|
| Category          | 21426-9001 K (NOT KA,KM,KX) |
| Discount Schedule | CS1                         |
| Returnability     | No                          |
| Country Of Origin | MX                          |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.