





SELECTOR SWITCH OPERATOR 30MM T-K

9001KS54FB

! Discontinued on: Jan 23, 2021

① Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Range Of Product | Harmony 9001KS |
|---------------------------|------------------------------------|
| Product Or Component Type | Selector switch |
| Device Short Name | 9001KS |
| Type Of Operator | Both sides to centre spring return |
| Operator Profile | Black gloved hand knob |

Complementary

| Bezel Material | Chromium plated metal |
|-------------------------------|------------------------|
| Mounting Diameter | 1.18 in (30 mm) |
| Net Weight | 0.54 lb(US) (0.245 kg) |
| Shape Of Signaling Unit Head | Round |
| Operator Position Information | 3 positions |
| Contacts Type And Composition | Without contact block |
| Mechanical Durability | 500000 cycles |
| Device Presentation | Basic element |

Environment

| Protective Treatment | TC |
|---------------------------------------|--|
| Ambient Air Temperature For Storage | -40158 °F (-4070 °C) |
| Ambient Air Temperature For Operation | -13158 °F (-2570 °C) |
| Overvoltage Category | Class II IEC 61140 |
| Ip Degree Of Protection | IP66 IEC 60529 |
| Nema Degree Of Protection | NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 4 NEMA 6 |
| Standards | JIS C 852 EN/IEC 60947-5-1 JIS C 4520 CSA C22.2 No 14 EN/IEC 60947-1 UL 508 EN/IEC 60947-5-4 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Product Certifications | UL 508 NEMA |
|------------------------|----------------------------|
| Vibration Resistance | 7 gn 2500 Hz)IEC 60068-2-6 |
| Shock Resistance | 50 an IEC 60068-2-27 |

Ordering and shipping details

| Category | US10CS121426 |
|-------------------|----------------|
| Discount Schedule | 0CS1 |
| Gtin | 00785901398530 |
| Returnability | No |
| Country Of Origin | MX |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |