# Product data sheet

Specifications





Selector switch head, Harmony 9001K, metal, long handle, black, 30mm, 4 positions, stay put

9001KS88FB

Product availability: Stock - Normally stocked in distribution facility

### Price\*: 53.00 USD

## Main

Range Of Product	Harmony 9001K
Product Or Component Type	Head for selector switch
Device Short Name	9001K
Type Of Operator	stay put
Operator Profile	Black long handle

## Complementary

Complementary	
Bezel Material	Metal
Mounting Diameter	1.18 in (30 mm)
Net Weight	0.38 lb(US) (0.172 kg)
Shape Of Signaling Unit Head	Octagonal
Operator Position Information	4 positions
Contacts Type And Composition	Without contact block
Mechanical Durability	500000 cycles
Product Compatibility	9001KA1 side 1 and 2
Device Presentation	Basic element
Cap/Operator Or Lens Colour	Black
Operator Profile	Long handle
Type Of Operator	Stay put
Size	30 mm
Cam Profile	8

## Environment

Protective Treatment	тс
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Nema Degree Of Protection	NEMA 1
	NEMA 12
	NEMA 13
	NEMA 2
	NEMA 3
	NEMA 3R
	NEMA 4
Standards	UL 508
	EN/IEC 60947-5-4
	JIS C 852
	CSA C22.2 No 14
	JIS C 4520
	EN/IEC 60947-5-1
	EN/IEC 60947-1
Product Certifications	UL 508
	NEMA
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27

## Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901959250
Returnability	Yes
Country Of Origin	US

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.13 in (5.4 cm)
Package 1 Width	1.81 in (4.6 cm)
Package 1 Length	3.90 in (9.9 cm)
Package 1 Weight	4.41 oz (125.0 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	20
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	10.51 lb(US) (4.765 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Mercury Free

Rohs Exemption Information
Yes


## **Certifications & Standards**


Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.			
Circularity Profile	No need of specific recycling operations			
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			

## Product data sheet

#### **Dimensions Drawings**

#### Dimensions






e panel thickness: 1 to 6 mm / 0.04 to 0.24 in.

#### Mounting and Clearance

#### **Contact Block Mounting Position**

Top and Rear views



(1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)

- (2) Operator
- (3) Locating notch


(4) Side 1

(5) Side 2

## Product data sheet

#### Panel Cut-Out

#### Clearance



Legend plate	a min.		b min.	
	mm	in.	mm	in.
9001KN2••	57.2	2.25	44.5	1.75
9001KN3••	57.2	2.25	50.8	2.00

#### Individual Cut-outs Details

2 alternatives

