





30mm push button, Type K, push to test pilot light, yellow LED light module, 120VAC, amber fresnel lens, NEMA 4, 13

9001KT1LYA31

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 197.00 USD

#### Main

Range Of Product	Harmony 9001K
Product Or Component Type	Push-to-test pilot light
Device Short Name	9001K

### Complementary

Metal
1.18 in (30 mm)
Round
Fresnel plastic
Amber
Yellow LED
BA 9s
Via integral transformer 110120 V AC 50/60 Hz 6 V)
Screw clamp terminals, 1 x 0.222 x 1.5 mm² IEC 60947-1
7.08 lbf.in (0.8 N.m) IEC 60947-1
Cross slotted
Any position
250 V 2)IEC 60947-1
2.5 kV IEC 60947-1
10 A cartridge fuse IEC 60947-5-1
LED
10 A
2.13 in (54 mm)
2.76 in (70 mm)
1.65 in (42 mm)
Push-to-test
0.46 lb(US) (0.21 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[Us] Rated Supply Voltage	110120 V
Light Block Supply	Via integral transformer
Light Source Colour	Yellow
Contacts Type And Composition	1 C/O
Supply Frequency	5060 Hz
Lens Material	Polycarbonate
Size	30 mm

### **Environment**

Standards	UL 508 EN/IEC 60947-5-4 EN/IEC 60947-5-1 JIS C8201-5-1 CSA C22.2 No 14 EN/IEC 60947-1 JIS C 852 JIS C8201-1
Product Certifications	UL 508 NEMA
Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27
Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 3R NEMA 4 NEMA 6

# Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901464020
Returnability	No
Country Of Origin	MX

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.08 in (12.903 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)
Package 1 Weight	6.40 oz (181.437 g)

## **Contractual warranty**

Warranty

Apr 25, 2024

18 months

### Sustainability Screen Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
<b>Environmental Disclosure</b>	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations  Circularity Profile