SQUARE D





# CONTROL STATION + OPERATORS

9001KYSK203

! Discontinued on: May 19, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range Of Product	Harmony 9001KY	
Product Or Component Type	Control station	
Device Short Name	9001KY	
Provided Equipment	Label plate START-STOP	
Contact Block Name	KA1 KA3	
Product Specific Application	For hoisting and mechanical handling applications	
Level Or Class	Class II Division 2 Group G Class III	

## Complementary

Enclosure/Cubicle Description	Wall-mounted enclosure 2 cut-outs Ø 30 mm	
Enclosure Material	Stainless Steel	
Type Of Installation	Indoor/outdoor	
Control Station Composition	2 push-buttons 1 NO + 2 NC	
Mechanical Interlocking	Without mechanical interlock	
Connector Type	Screw clamp connector	
Connections - Terminals	Direct connection AWG 2) solid stranded Direct connection AWG 12) solid stranded Direct connection AWG 24) solid stranded	
[Ue] Rated Operational Voltage	300 V	
[le] Rated Operational Current Ac	10 A	

#### **Environment**

Nema Degree Of Protection	NEMA 3 NEMA 13 NEMA 4 NEMA 1
Environmental Characteristic	Dust and oil resistant Resistant against immersion in water
Product Certifications	UL Listed
Ambient Air Temperature For Operation	-13140 °F (-2560 °C)
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# Ordering and shipping details

Category	US10CS121426	
Discount Schedule	0CS1	
Gtin	785901040095	
Returnability	No	
Country Of Origin	MX	

# **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	10.16 in (25.806 cm)	
Package 1 Width	4.00 in (10.16 cm)	
Package 1 Length	25.81 in (65.548 cm)	
Package 1 Weight	3.50 lb(US) (1.588 kg)	

## **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov