Product data sheet

Specifications



Control Station -Type K-30mm-10A -300V-1 Operator- 1 N.C-STOP

9001KYSS103

() Discontinued on: Jan 23, 2021

Main

mann		
Range Of Product	Harmony 9001KY	
Product Or Component Type	Control station	
Device Short Name	9001KY	
Provided Equipment	Label plate STOP	
Contact Block Name	КАЗ	
Product Specific Application	For hoisting and mechanical handling applications	
Level Or Class	Class II Division 2 Group G Class III	

Complementary

Enclosure/Cubicle Description	Wall-mounted enclosure 1 cut-out Ø 30 mm
Enclosure Material	Stainless Steel
Type Of Installation	Indoor/outdoor
Control Station Composition	1 push-button momentary 1 NC
Mechanical Interlocking	Without mechanical interlock
Connector Type	Screw clamp connector
Connections - Terminals	Direct connection AWG 2) solid stranded Direct connection AWG 12) solid stranded Direct connection AWG 24) solid stranded
[Ue] Rated Operational Voltage	300 V
[le] Rated Operational Current Ac	10 A

Environment

Nema Degree Of Protection	NEMA 3 NEMA 4 NEMA 1 NEMA 13
Environmental Characteristic	Dust and oil resistant Resistant against immersion in water
Product Certifications	UL Listed
Ambient Air Temperature For Operation	-13140 °F (-2560 °C)
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Category	21426-9001 K (NOT KA,KM,KX)	
Discount Schedule	CS1	
Returnability	No	
Country Of Origin	MX	

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov