





Double-headed push-button head, Harmony 9001SK, plastic, flush, 7 colours choice, 30mm, stay put, with mechanical interlocking

9001SKR11U

Product availability: Stock - Normally stocked in distribution facility

Price*: 120.00 USD

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Head for double-headed push-button
Device Short Name	9001SK

Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Cad Overall Width	1.81 in (46 mm)
Cad Overall Height	1.77 in (45 mm)
Cad Overall Depth	2.72 in (69 mm)
Net Weight	0.21 lb(US) (0.095 kg)
Operating Position	Any position
Shape Of Signaling Unit Head	Round
Type Of Operator	maintained
Operator Profile	mushroom Ø 30 mm, unmarked
Mechanical Durability	5000000 cycles
Cap/Operator Or Lens Colour	7 colours choice
Operator Profile	Flush
Type Of Operator	Stay put
Contacts Type And Composition	Without contact block
Size	30 mm
Mechanical Interlocking	With mechanical interlocking

Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 3 NEMA 4 NEMA 4
Standards	CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60947-1 EN/IEC 60947-5-4 JIS C 4520 JIS C 852 UL 508
Product Certifications	UL listed file E78403 CCN NKCR CSA LR25490 class 3211 03 NEMA UL 508
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27

Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901546634
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.43 in (29.032 cm)
Package 1 Width	4.50 in (11.43 cm)
Package 1 Length	29.03 in (73.742 cm)
Package 1 Weight	5.44 oz (154.221 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
Ø	Mercury Free	
9	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov