

# Product data sheet

Specifications



Push-to-test pilot light head,  
Harmony 9001SK, plastic, without  
cap, 30mm, 24-28V

9001SKT35

Product availability: Stock - Normally stocked in distribution facility

Price\*: 237.00 USD

## Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Head for push-to-test pilot light
Light Block Supply	Full voltage 24 V Full voltage 28 V

## Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Round
Cap/Operator Or Lens Colour	Without cap
Bulb Base	BA 9s
Operating Mode	Push-to-test
[Us] Rated Supply Voltage	24...28 V
Light Block Supply	Full voltage
Contacts Type And Composition	1 C/O
Size	30 mm
Light Source	Incandescent bulb

## Environment

Protective Treatment	TC
Ip Degree Of Protection	IP66

## Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901959939
Returnability	Yes
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	2.30 in (5.842 cm)
Package 1 Width	2.00 in (5.080 cm)
Package 1 Length	4.50 in (11.430 cm)
Package 1 Weight	4.16 oz (117.900 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	9
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	2.78 lb(US) (1.261 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	288
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	106.60 lb(US) (48.355 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™** label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations <a href="#">Circularity Profile</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>