

Product data sheet

Specifications

SQUARE D



Pneumatic Timer - off delay - 0.1-60 seconds - 24VDC - DPDT

9050HO20DV53

Discontinued on: Oct 11, 2019

Discontinued

Main

Product Range	9050A/H
Product Type	Timer
Timing Mode	Off-delay
Timing Range	0.15 s...1 min
Switch Function	DPDT
Coil Voltage	24 V DC
Contact Operation	Time delayed 2 NO + 2 NC
Current Rating	10 A

Complementary

Maximum Switching Voltage	250 V DC
Electrical Connection	Screw-clamp terminals
Reset Response Time	50 ms - on-delay 70 ms - off-delay
Mounting Support	Panel

Environment

Ambient Temperature Range - Operational	68...104 °F (20...40 °C)
Certifications	CSA UL Listed
Height	2.95 in (75 mm)
Width	4.72 in (120 mm)
Depth	3.74 in (95 mm)

Ordering and shipping details

Category	21635-9050 C,H DC PNEUMATIC TIMERS
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

